













The DNA of tech.™



Diodes / Rectifiers in eSMP® Series

(enhanced surface mount power packages)

<p>MicroSMF (DO-219AC)</p> <p>Flat-Lead Package with Low Profile Height of < 0.6 mm</p>  <p>Useful links: Zener Diodes</p>	<p>MicroSMP (DO-219AD)</p> <p>Space-Saving Footprint with Typical Height of 0.65 mm</p>  <p>Useful links: Schottky Rectifiers Standard / Fast Recovery TVS Ultrafast Recovery</p>	<p>SMF (DO-219AB)</p> <p>Low-Profile Package with 1 mm Height</p>  <p>Useful links: ESD Protection Diodes Schottky Rectifiers Standard / Fast Recovery TVS Ultrafast Recovery Zener Diodes</p>	<p>SMP (DO-220AA)</p> <p>Space-Saving Footprint with Typical Height of 1 mm</p>  <p>Useful links: Schottky Rectifiers Standard / Fast Recovery TVS Ultrafast Recovery Zener Diodes</p>	<p>SlimSMAW (DO-221AD)</p> <p>Footprint Compatible with SOD-128; Typical Height 1.0 mm</p>  <p>Useful links: Schottky Rectifiers TVS Ultrafast Recovery</p>
<p>SMPD (TO-263AC)</p> <p>Footprint Compatible with D²PAK, 1.7 mm Typ. Height</p>  <p>Useful links: Schottky Rectifiers Standard / Fast Recovery Ultrafast Recovery</p>	<p>SlimDPAK (TO-252AE)</p> <p>Low-Profile Package with Typical Height of 1.3 mm</p>  <p>Useful links: Schottky Rectifiers Standard / Fast Recovery Ultrafast Recovery</p>	<p>SMPC (TO-277A)</p> <p>Small Footprint and Low Profile Height of 1.1 mm</p>  <p>Useful links: Schottky Rectifiers Standard / Fast Recovery TVS Ultrafast Recovery</p>	<p>SMPA (DO-221BC)</p> <p>Very Low Profile Height of 0.95 mm</p>  <p>Useful links: Schottky Rectifiers Standard / Fast Recovery</p>	<p>SlimSMA (DO-221AC)</p> <p>Very Low Profile Height of 0.95 mm (typical)</p>  <p>Useful links: Schottky Rectifiers Standard / Fast Recovery TVS Ultrafast Recovery</p>

Note:

- Schottky Rectifiers include TMBS® (Trench MOS Barrier Schottky)
- Ultrafast Recovery includes FRED Pt®

