

CloudHawk GPS Asset Tracking Solution

**A High Performance,
Trusted, GPS Asset
Tracking Solution that
Gives You More**



CloudHawk is an innovative and high performance GPS tracking solution that provides real-time, visibility into your business assets, allowing quick decision-making to increase productivity. CloudHawk can connect to all types of assets and provides real-time location and sensor data insights. CloudHawk UltraSense GPS technology enables you to get a signal where other monitoring solutions simply don't, even when hidden and placed in hard to find locations, eliminating the need for line-of-sight for continued tracking.

CloudHawk dramatically decreases the risk of theft and loss through customized geofences and notification alerts sent to your mobile devices that let you know instantly if an asset is moved without authorization, helping to greatly reduce recovery time.



Construction
Equipment

Fleets

Non-Powered
Assets & Cargo

Trailers


Vehicles

Key Benefits:

- > Increase operational efficiency from real-time visibility of all assets
- > Make fast business decisions and responses to real-time alerts and notifications
- > Decrease operating costs by monitoring asset usage, reducing excess idle time or other cost causing activities
- > Increase revenue from operational efficiency, increased ability to properly invoice customers
- > Reduce theft costs and increased insurance premiums by detecting and responding immediately to theft and sensor alert indicators
- > Reduce risk and costs of cargo spoilage and load rejection by responding to real-time notifications of temperature and other sensor alerts
- > Optimize maintenance costs by leveraging precise tracking mileage, engine hours to prioritize when to schedule servicing – preventing over and under servicing of assets

CloudHawk GPS Asset Tracking Solution

Features	CH300	CH301	CH311	CH320
Cellular	2G/3G	2G/3G	2G/3G	2G/3G
Waterproof	Yes	Yes	No	Yes
Battery Capacity	90 days standby 1 week constant movement	90 days standby 1 week constant movement	90 days standby 1 week constant movement	90 days standby 1 week constant movement
Charging Alternatives	DC Power 8-40V	DC Power 8-40V	USB	Wireless Charging
Ability to Add Sensors	Wired and Wireless	Wireless Only	Wireless Only	Wireless Only
Size	100mm x 100mm x 33mm 3¾" x 3¾" x 1¼"	100mm x 100mm x 33mm 3¾" x 3¾" x 1¼"	100mm x 100mm x 33mm 3¾" x 3¾" x 1¼"	100mm x 100mm x 33mm 3¾" x 3¾" x 1¼"



Arrow Electronics Inc.
9201 East Dry Creek road
Centennial, CO 80112,
USA

Ordering Information

Contact Arrow for part numbers and a quote

Email

iot@arrow.com

Online

www.arrow.com/IoT